Assembly Instructions - External Wall Plate

IMPORTANT! Read entire instruction sheet before you start installation and assembly.

Models OP-WSP 450, OP-WSP 460, OP-WSP 470

A WARNING

 Make sure that the wall will safely support the combined load of the equipment and all attached hardware and components.

PARTS LIST						
MODEL#						
420	460	470				
OP-WSP450	OP-WSP460	OP-WSP470				
Š	ڄ	>				
О	О	О		PART#	QTY.	DESCRIPTION
✓			Α	024-1014	1	wall plate 16" centers (black)
	✓			024-1015		wall plate 20" centers (black)
		✓		024-1016		wall plate 24" centers (black)
✓	✓	✓	В	510-9108	8	1/4-20 x 1/2" phillips screw
✓	✓	✓	С	520-9521	12	1/4-20 x 2 1/2" phillips screw
✓	✓	✓	D	590-1093	12	toggler
✓	✓	✓	Е	540-9440	8	washer




MAXIMUM OSHPD LOAD CAPACITY: 162 lb (73.5 kg)

OP-WSP 450 for studs on 16" (406 mm) centers, contains two electrical box knockouts.


OP-WSP 460 for studs on 20" (508 mm) centers, contains two electrical box knockouts.


OP-WSP 470 for studs on 24" (610 mm) centers, contains two electrical box knockouts.













*Note: The mounting hole which is closest to the lip of the plate indicates the up position.


Note: Wall plate may appear slightly different than illustrated.




Use wall plate (A) as a template to mark slot centers on stud centers.




Drill twelve 3/4" (19 mm) dia. holes through drywall and studs. Insert togglers (**D**) as shown below.







A WARNING

- Make sure that mounting screws are anchored into the center of the studs. The use of an "edge to edge" stud finder is highly recommended.
- Place screw (C) through wall plate (A). Partially fasten the toggler (D) to the back of the screw. Pivot ends of toggler (D) 90°.







Push toggler (**D**) through hole. Pull screw (**C**) back untill toggler (**D**) hits the inside of the metal stud.



Fasten all twelve screws (C) tight, untill wall plate (A) is flush with wall.



Note: See below for proper holes to attach mount to wall plate.



For customer service call 1-800-729-0307 or 708-865-8870.